

Garant**SNMM 190624, Grade: HB7010-1**

Order data

Order number	251394 HB7010-1
GTIN	4045197780188
Item class	21G

Description

SNMM 190624 HB7010-1 Corner radius: 2.4 mm
Grade: HB7010-1
Chip breaker: SR
Cutting depth a_p : 2 - 12 mm
Feed f : 0.4 - 1.2 mm/rev.
Cutting speed v_c main application: 100 - 375 m/min

Technical description

Cutting speed v_c main application	100 - 375 m/min
Chip breaker	SR
Cutting conditions	continuous
Corner radius	2.4 mm
Grade	HB7010-1
Cutting depth a_p	2 - 12 mm
Feed f	0.4 - 1.2 mm/rev.

Main application	P
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMM 190624
Number of changes/inserts	8
Type of product	Indexable insert for turning