

**Garant**
**TNMG 160404, Grade: HB7010-1**


### Order data

Order number	251432 HB7010-1
GTIN	4045197780195
Item class	21G

### Technical description

Cutting conditions	continuous
Corner radius	0.4 mm
Chip breaker	SS
Cutting speed $v_c$ main application	150 - 500 m/min
Feed $f$	0.1 - 0.4 mm/rev.
Grade	HB7010-1
Cutting depth $a_p$	0.3 - 2 mm
Main application	P
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	TNMG 160404
Number of changes/inserts	6

Type of product

Indexable insert for turning