

Garant**VNMG 160408, Grade: HB7010-1**

Order data

Order number	251804 HB7010-1
GTIN	4045197780263
Item class	21G

Description

VN.G 160408 HB7010-1 Grade: HB7010-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 4 mm
Feed f : 0.1 - 0.5 mm/rev.
Cutting speed v_c main application: 120 - 440 m/min

Technical description

Grade	HB7010-1
Cutting depth a_p	0.5 - 4 mm
Cutting speed v_c main application	120 - 440 m/min
Main application	P
Cutting conditions	continuous
Corner radius	0.8 mm

Chip breaker	SM
Feed f	0.1 - 0.5 mm/rev.
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	VNMG 160408
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning