

Garant
WNMG 060404, Grade: HB7010-1


Order data

Order number	251952 HB7010-1
GTIN	4045197780270
Item class	21G

Technical description

Main application	P
Feed f	0.1 - 0.4 mm/rev.
Corner radius	0.4 mm
Cutting speed v_c main application	150 - 500 m/min
Cutting depth a_p	0.3 - 2 mm
Cutting conditions	continuous
Chip breaker	SS
Grade	HB7010-1
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	WNMG 080404
Number of changes/inserts	6

Type of product

Indexable insert for turning