

Garant
WNMG 060408, Grade: HB7010-1


Order data

Order number	251954 HB7010-1
GTIN	4045197780287
Item class	21G

Description

WNMG 060408 HB7010-1 Grade: HB7010-1
 Chip breaker: SS
 Cutting depth a_p : 0.3 - 2 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 150 - 500 m/min

Technical description

Chip breaker	SS
Cutting conditions	continuous
Cutting depth a_p	0.3 - 2 mm
Feed f	0.1 - 0.4 mm/rev.
Main application	P
Grade	HB7010-1
Corner radius	0.8 mm
Cutting speed v_c main application	150 - 500 m/min

Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	WNMG 060408
Number of changes/inserts	6
Type of product	Indexable insert for turning