

Garant**CC.T 060202, Grade: HB7010-1**

Order data

Order number	260050 HB7010-1
GTIN	4045197780386
Item class	21G

Description

CCMT 060202 HB7010-1 Grade: HB7010-1
Chip breaker: SS
Tolerance: M
Cutting depth a_p : 0.2 - 2.5 mm
Feed f : 0.05 - 0.25 mm/rev.
Cutting speed v_c main application: 150 - 500 m/min

Technical description

Feed f	0.05 - 0.25 mm/rev.
Cutting conditions	continuous
Grade	HB7010-1
Cutting depth a_p	0.2 - 2.5 mm
Main application	P
Chip breaker	SS

Cutting speed v_c main application	150 - 500 m/min
Corner radius	0.2 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	CCMT 060202
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning