

Garant
CC.T 09T302, Grade: HB7010-1


Order data

| | |
|--------------|-----------------|
| Order number | 260148 HB7010-1 |
| GTIN | 4045197780461 |
| Item class | 21G |

Description

CC.T 09T302 HB7010-1 Grade: HB7010-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.2 - 4 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

| | |
|--------------------------------------|-------------------|
| Cutting depth a_p | 0.2 - 4 mm |
| Feed f | 0.1 - 0.3 mm/rev. |
| Corner radius | 0.2 mm |
| Cutting speed v_c main application | 120 - 440 m/min |
| Chip breaker | SM |
| Grade | HB7010-1 |
| Cutting conditions | continuous |

| | |
|-------------------------------|------------------------------------|
| Main application | P |
| Finishing/roughing assignment | Skrubbearbejdning-sletbearbejdning |
| Tool material | Carbide |
| ISO code indexable insert | CCMT 09T302 |
| Number of changes/inserts | 2 |
| Tolerance | M |
| Type of product | Indexable insert for turning |