



High feed rate milling cutter 7792VX, Plain shank, $\varnothing D$ / number of teeth Z: 32/3Lmm



Order data

Order number	221900 32/3L
GTIN	2050002058484
Item class	28R

Description

Description:

The unique design of the indexable inserts together with their approach angle in the milling body greatly reduces the radial forces and diverts them into the axial direction. Particularly thick indexable inserts with 4 cutting edges for the heaviest duties and high cost-effectiveness. The tool has particular advantages for face milling and milling deep pockets. With its ground wiper chamfer it is equally well suited also to plunge milling and finish milling operations.

Technical description

Cutting edge $\varnothing D_c$	32 mm
Overhang L_1	70 mm
Indexable insert size	12
suitable indexable insert	XD..
Insert screw	229908 (T15; 3.1 Nm)
maximum cutting depth $a_{p\max}$	2.5 mm
Overall length L_{tot}	250 mm
Number of cutting edges Z	3
Shank $\varnothing D_s$ h6	32 mm
$\varnothing D_3$	11 mm
Through-coolant	yes
Circular interpolation milling $\varnothing D_{\max}$	62 mm

Circular interpolation milling $\varnothing D_{\min}$	43 mm
Ramping angle α_{\max}	1.67 degrees
Ramping length L for α_{\max}	10.3 mm
Setting angle κ	12 degrees
Shank type	Plain shank
Milling application	Circular milling
Milling application	Ramping
Milling application	Plunging
Machining strategy	HPC
Type of product	Copy mill

Accessories

Clamping screw	229908
----------------	--------