

Garant
TCMT 16T308, Grade: HB7010-1


Order data

Order number	260988 HB7010-1
GTIN	4045197780737
Item class	21G

Description

TCMT 16T308 HB7010-1 Grade: HB7010-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.5 - 2.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Grade	HB7010-1
Main application	P
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 440 m/min
Cutting depth a_p	0.5 - 2.5 mm
Corner radius	0.8 mm
Cutting conditions	continuous
Chip breaker	SM

Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	TCMT 16T308
Number of changes/inserts	3
Tolerance	M
Type of product	Indexable insert for turning