

Garant**VBMT 110302, Grade: HB7010-1**

Order data

Order number	261142 HB7010-1
GTIN	4045197780744
Item class	21G

Technical description

Grade	HB7010-1
Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	150 - 500 m/min
Corner radius	0.2 mm
Cutting conditions	continuous
Chip breaker	SS
Main application	P
Feed f	0.05 - 0.2 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	VBMT 110302

Number of changes/inserts	2
Type of product	Indexable insert for turning