

## Garant

### GARANT Master Steel PickPocket solid carbide roughing end mill HPC, TiAlN, Ø f8 DC: 6,7mm



#### Order data

Order number	202404 6,7
GTIN	4045197779267
Item class	11X

#### Description

##### Version:

For **roughing and finishing**

With corner radii similar to torus cutters.

Up to  $1 \times D$  into solid material **at very high feed rates** with smooth cutting action.

##### Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

#### Technical description

Cutting edge $\varnothing D_c$	6.7 mm
Recess $\varnothing D_1$	6.5 mm
Flute length $L_c$	16 mm
Feed $f_z$ for side milling in steel $< 900 \text{ N/mm}^2$	0.05 mm
Shank $\varnothing D_s$	8 mm
No. of teeth $Z$	3
Feed $f_z$ for slot milling in steel $< 900 \text{ N/mm}^2$	0.04 mm
Shank	DIN 6535 HB to h6
Overall length $L$	63 mm
Tolerance nominal $\varnothing$	f8
Direction of infeed	horizontal, oblique and vertical

Overhang length $L_1$ incl. recess	25 mm
Helix angle	38 degrees
Corner rounding $r_v$	0.34 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	0.4×D for side milling
Cutting width $a_e$ for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	260 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	190 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	150 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	80 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	70 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable