

Garant
GARANT Master Steel PickPocket solid carbide roughing end mill HPC, TiAlN, Ø f8 DC: 7mm

Order data

Order number	202406 7
GTIN	4045197781376
Item class	11X

Description
Version:

For **roughing and finishing**

With corner radii similar to torus cutters.

Up to 1×D into solid material **at very high feed rates** with smooth cutting action.

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Technical description

Flute length L_c	16 mm
Recess $\varnothing D_1$	6.7 mm
Tolerance nominal \varnothing	f8
Cutting edge $\varnothing D_c$	7 mm
Feed f_z for slot milling in steel < 900 N/mm ²	0.04 mm
Shank	DIN 6535 HB to h6
No. of teeth Z	3
Overhang length L_1 incl. recess	30 mm
Direction of infeed	horizontal, oblique and vertical
Shank $\varnothing D_s$	8 mm
Overall length L	68 mm

Feed f_z for side milling in steel $< 900 \text{ N/mm}^2$	0.05 mm
Helix angle	38 degrees
Corner rounding r_v	0.35 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	$0.4 \times D$ for side milling
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel $< 500 \text{ N/mm}^2$	suitable	260 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	240 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	190 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	180 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable only under restricted conditions	150 m/min	P
INOX $< 900 \text{ N/mm}^2$	suitable	80 m/min	M
INOX $> 900 \text{ N/mm}^2$	suitable	70 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable