

Garant
DNMG 110404, Grade: HB7010-1


Order data

Order number	250652 HB7010-1
GTIN	4045197779823
Item class	21G

Description

DNMG 110404 HB7010-1 Grade: HB7010-1
 Chip breaker: SS
 Cutting depth a_p : 0.3 - 2 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 150 - 500 m/min

Technical description

Cutting depth a_p	0.3 - 2 mm
Main application	P
Feed f	0.1 - 0.4 mm/rev.
Cutting speed v_c main application	150 - 500 m/min
Chip breaker	SS
Corner radius	0.4 mm
Cutting conditions	continuous

Grade	HB7010-1
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DNMG 110404
Number of changes/inserts	4
Type of product	Indexable insert for turning