

Garant**DNMG 110404, Grade: HB7010-1****Order data**

Order number	250752 HB7010-1
GTIN	4045197779861
Item class	21G

Description

DNMG 110404 HB7010-1 Grade: HB7010-1
Chip breaker: SM
Tolerance: M
Cutting depth a_p : 0.5 - 5 mm
Feed f : 0.2 - 0.5 mm/rev.
Cutting speed v_c main application: 120 - 440 m/min

Technical description

Main application	P
Chip breaker	SM
Grade	HB7010-1
Cutting speed v_c main application	120 - 440 m/min
Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.5 - 5 mm

Corner radius	0.4 mm
Cutting conditions	continuous
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	DNMG 110404
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning