


Garant
SNMG 190616, Grade: HB7010-1


Order data

Order number	251238 HB7010-1
GTIN	4045197780096
Item class	21G

Description

SNMG 190616 HB7010-1 Corner radius: 1.6 mm
 Grade: HB7010-1
 Chip breaker: SM
 Cutting depth a_p : 0.5 - 6 mm
 Feed f : 0.15 - 0.5 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Cutting conditions	continuous
Cutting depth a_p	0.5 - 6 mm
Corner radius	1.6 mm
Cutting speed v_c main application	120 - 440 m/min
Main application	P
Grade	HB7010-1
Feed f	0.15 - 0.5 mm/rev.

Chip breaker	SM
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	SNMG 190616
Number of changes/inserts	8
Type of product	Indexable insert for turning