

**Garant**
**Die 6g, M: M4,5**


### Order data

Order number	140300 M4,5
GTIN	4062406189358
Item class	11K

### Description

**Version:**

Closed, pre-slit form. **≥ M3 with tapered lead chamfer** on both sides for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Cutting direction: right-hand

Tolerance class: DIN 13 6g

Pitch: 0.75 mm

External Ø: 20 mm

Height: 7 mm

### Technical description

Tolerance class	DIN 13 6g
Height	7 mm
Pitch	0.75 mm
External Ø	20 mm
Thread size	M4.5

Thread type	M
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Cutting direction	right-hand
Type of product	Die

### User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		