

Garant
SNMG 190616, Grade: HB7010-1


Order data

Order number	251336 HB7010-1
GTIN	4045197780140
Item class	21G

Description

SNMG 190616 HB7010-1 Corner radius: 1.6 mm
 Grade: HB7010-1
 Chip breaker: SG
 Cutting depth a_p : 1.5 - 9 mm
 Feed f : 0.25 - 0.8 mm/rev.
 Cutting speed v_c main application: 100 - 375 m/min

Technical description

Chip breaker	SG
Cutting conditions	continuous
Feed f	0.25 - 0.8 mm/rev.
Corner radius	1.6 mm
Main application	P
Cutting speed v_c main application	100 - 375 m/min
Cutting depth a_p	1.5 - 9 mm

Grade	HB7010-1
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	SNMG 190616
Number of changes/inserts	8
Type of product	Indexable insert for turning