

Garant**VNMG 160404, Grade: HB7010-1**

Order data

Order number	251802 HB7010-1
GTIN	4045197780256
Item class	21G

Technical description

Main application	P
Feed f	0.1 - 0.5 mm/rev.
Cutting speed v_c main application	120 - 440 m/min
Cutting conditions	continuous
Grade	HB7010-1
Chip breaker	SM
Corner radius	0.4 mm
Cutting depth a_p	0.5 - 4 mm
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	VNMG 160404

Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning