

Garant**Die, UNC: 9/16-12**

Order data

Order number	142520 9/16-12
GTIN	4062406189556
Item class	11K

Description

Version:

Closed, pre-slit form; **with tapered lead chamfer on both sides** for easy start to the threading action and clean swarf evacuation in the direction of cutting. **1¾ turns lead chamfer.**

Application:

For UNC uniform coarse threads ASME – B1.1.

Tolerance class: 2A

Threads per inch: 12

Thread Ø: 14.29 mm

External Ø: 38 mm

Height: 14 mm

Technical description

Thread Ø	14.29 mm
Threads per inch	12
External Ø	38 mm
Height	14 mm

Thread size	9/16-12 UNC
Cutting direction	right-hand
Thread type	UNC
Flank angle	60 °
Tool material	HSS
Standard	EN 22568
Tolerance class	2A
Type of product	Die

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Oil	suitable		
dry	suitable only under restricted conditions		