

Garant**WNMG 060404, Grade: HB7010-1**

Order data

Order number	252062 HB7010-1
GTIN	4045197780317
Item class	21G

Technical description

Grade	HB7010-1
Cutting conditions	continuous
Cutting depth a_p	0.5 - 4 mm
Cutting speed v_c main application	120 - 440 m/min
Chip breaker	SM
Feed f	0.2 - 0.5 mm/rev.
Corner radius	0.4 mm
Main application	P
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	WNMG 060404
Number of changes/inserts	6

Tolerance	M
Type of product	Indexable insert for turning