

Garant
WNMG 080404, Grade: HB7010-1


Order data

Order number	252068 HB7010-1
GTIN	4045197780331
Item class	21G

Description

WN.G 080404 HB7010-1 Grade: HB7010-1

Chip breaker: SM

Tolerance: M

 Cutting depth a_p : 0.5 - 4 mm

 Feed f : 0.2 - 0.5 mm/rev.

 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Feed f	0.2 - 0.5 mm/rev.
Chip breaker	SM
Main application	P
Cutting conditions	continuous
Corner radius	0.4 mm
Cutting speed v_c main application	120 - 440 m/min
Cutting depth a_p	0.5 - 4 mm

Grade	HB7010-1
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	WNMG 080404
Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning