

**Garant****WNMG 080408, Grade: HB7010-1**

## Order data

Order number	252208 HB7010-1
GTIN	4045197780362
Item class	21G

## Technical description

Cutting depth $a_p$	1.5 - 6 mm
Corner radius	0.8 mm
Cutting speed $v_c$ main application	100 - 375 m/min
Main application	P
Grade	HB7010-1
Feed $f$	0.25 - 0.6 mm/rev.
Chip breaker	SG
Cutting conditions	continuous
Finishing/roughing assignment	Roughing
Tool material	Carbide
ISO code indexable insert	WNMG 080408
Number of changes/inserts	6

Type of product

Indexable insert for turning