

Garant

Indexable insert for turning CC.T 09T308, for medium machining, Grade: HB7010-1

**Order data**

Order number	260152 HB7010-1
GTIN	4045197780485
Item class	21G

Technical description

Cutting speed v_c main application	120 - 440 m/min
Chip breaker	SM
Feed f	0.1 - 0.3 mm/rev.
Grade	HB7010-1
Cutting conditions	continuous
Corner radius	0.8 mm
Main application	P
Cutting depth a_p	0.2 - 4 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide

ISO code indexable insert	CCMT 09T308
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning