

Garant
CC.T 120408, Grade: HB7010-1


Order data

Order number	260160 HB7010-1
GTIN	4045197780508
Item class	21G

Description

CC.T 120408 HB7010-1 Grade: HB7010-1
 Chip breaker: SM
 Tolerance: M
 Cutting depth a_p : 0.2 - 4 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 120 - 440 m/min

Technical description

Chip breaker	SM
Main application	P
Cutting speed v_c main application	120 - 440 m/min
Feed f	0.1 - 0.3 mm/rev.
Grade	HB7010-1
Corner radius	0.8 mm
Cutting depth a_p	0.2 - 4 mm

Cutting conditions	continuous
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	CCMT 120408
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning