

Ansell
Pair of cut-resistant heat resistant gloves ActivArmr 70-765, Glove size: 9

Order data

Order number	094622 9
GTIN	10076490440241
Item class	04P

Description
Version:

Vantage® 70-765. Kevlar® cut-resistant gloves combined with high-quality leather on the palms. With **reinforced thumbs** and seams on the back of the fingers for increased protection against cuts. Suitable for taking workpieces (e.g. sheet metal) from robot welding workplaces.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.

Cut protection class: D

Length: 235 mm

Technical description

Glove size	9
Type of glove	Heat protection gloves
Protection category	Category III
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	Flame resistance stage X

EN 388:2016	4X43D
EN 407	X1XXXX
Contact heat up to	200 °C
Backing material	Nylon, acrylic, Kevlar®
Coating variant	No coating
Colour	grey / green
Application	reusable
Length	235 mm
Contents	12
Washing	40 °C coloureds
Application range	All-round
Application range	Heavy Duty
Knitted technology	10G
Cut protection class	D
Weight	88.7 g
Type of product	Heat protection gloves