

**Garant****DC.T 11T302, Grade: HB7010-1**

## Order data

Order number	260356 HB7010-1
GTIN	4045197780539
Item class	21G

## Description

DCMT 11T302 HB7010-1 Grade: HB7010-1  
Chip breaker: SS  
Tolerance: M  
Cutting depth  $a_p$ : 0.2 - 1.5 mm  
Feed  $f$ : 0.05 - 0.2 mm/rev.  
Cutting speed  $v_c$  main application: 150 - 500 m/min

## Technical description

Cutting conditions	continuous
Cutting depth $a_p$	0.2 - 1.5 mm
Grade	HB7010-1
Corner radius	0.2 mm
Cutting speed $v_c$ main application	150 - 500 m/min
Feed $f$	0.05 - 0.2 mm/rev.

Main application	P
Chip breaker	SS
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DCMT 11T302
Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning