

Garant**DC.T 070202, Grade: HB7010-1****Order data**

Order number	260449 HB7010-1
GTIN	4045197780560
Item class	21G

Technical description

Cutting depth a_p	0.5 - 2.5 mm
Feed f	0.1 - 0.3 mm/rev.
Chip breaker	SM
Cutting conditions	continuous
Grade	HB7010-1
Cutting speed v_c main application	120 - 440 m/min
Main application	P
Corner radius	0.2 mm
Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	DCMT 070202

Number of changes/inserts	2
Tolerance	M
Type of product	Indexable insert for turning