

Garant
**GARANT Master Steel PickPocket solid carbide roughing end mill HPC, TiAlN,
 Ø f8 DC: 9,7mm**

Order data

Order number	202406 9,7
GTIN	4045197781420
Item class	11X

Description
Version:

For **roughing and finishing**

With corner radii similar to torus cutters.

Up to 1xD into solid material **at very high feed rates** with smooth cutting action.

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Technical description

Recess $\varnothing D_1$	9.4 mm
Shank	DIN 6535 HB to h6
Feed f_z for side milling in steel < 900 N/mm ²	0.08 mm
Overhang length L_1 incl. recess	38 mm
Shank $\varnothing D_s$	10 mm
Feed f_z for slot milling in steel < 900 N/mm ²	0.06 mm
Flute length L_c	22 mm
No. of teeth Z	3
Direction of infeed	horizontal, oblique and vertical
Overall length L	80 mm
Cutting edge $\varnothing D_c$	9.7 mm

Tolerance nominal \varnothing	f8
Helix angle	38 degrees
Corner rounding r_v	0.49 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.4×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	260 m/min	P
Steel < 750 N/mm ²	suitable	240 m/min	P
Steel < 900 N/mm ²	suitable	190 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	150 m/min	P
INOX < 900 N/mm ²	suitable	80 m/min	M
INOX > 900 N/mm ²	suitable	70 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable