


**Fabric velour-backed abrasive disc (CER), 115 mm Ø, Grit: 60****Order data**

Order number	567510 60
GTIN	4018875292068
Item class	56V

**Description****Version:**

The **back of the disc is covered with velour loops** which are self-attaching to **hook and loop fastener backing pads**, e.g. No. **567760** . For quick disc changing.

Velour-backed abrasive discs XK870K with sturdy **polyester fabric**. The **self-sharpening ceramic grit** with MIT active grinding layer (TOP Size) (**TOP Size**) ensures a cool and aggressive cut.

**Application:**

On **angle grinders** / eccentric grinders with hook and loop fastener pads (dust removal not available). Maximum working speed **40 m/s**.

For grinding all steels, particularly well suited to difficult to machine materials such as **stainless steel, nickel alloys, chromium, titanium**.

**Note:**

Suitable hand sanding block for hook and loop grinding discs see No. 567857 size 125 and Gr.150. See No. 566902 – 566950 for velour abrasive discs. For mini grinding systems Ø 50 mm and Ø 75 mm, see No. 554005 onwards.

**Technical description**

Grit	60
------	----

Disc Ø	115 mm
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	115 mm Ø
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable only under restricted conditions		
Paint	suitable only under restricted conditions		
dry	suitable		

## Accessories

Hook and loop polishing pad,M14 External Ø 115 mm	567762 115
Hook and loop backing pad,M14 External Ø 115 mm	567760 115

