

**Fabric velour-backed abrasive disc (CER), Ø 150 mm, Grit: 60****Order data**

|              |               |
|--------------|---------------|
| Order number | 567512 60     |
| GTIN         | 4018875483084 |
| Item class   | 56V           |

**Description****Version:**

The **back of the disc is covered with velour loops** which are self-attaching to **hook and loop fastener backing pads**, e.g. No. **567760** . For quick disc changing.

Velour-backed abrasive discs XK870K with sturdy **polyester fabric**. The **self-sharpening ceramic grit** with MIT active grinding layer (TOP Size) (**TOP Size**) ensures a cool and aggressive cut.

**Application:**

On **angle grinders** / eccentric grinders with hook and loop fastener pads (dust removal not available). Maximum working speed **40 m/s**.

For grinding all steels, particularly well suited to difficult to machine materials such as **stainless steel, nickel alloys, chromium, titanium**.

**Note:**

Suitable hand sanding block for hook and loop grinding discs see No. 567857 size 125 and Gr.150. See No. 566902 – 566950 for velour abrasive discs. For mini grinding systems Ø 50 mm and Ø 75 mm, see No. 554005 onwards.

**Technical description**

|        |        |
|--------|--------|
| Disc Ø | 150 mm |
|--------|--------|

|   |                             |
|---|-----------------------------|
| Grit                                    | 60                          |
| Grinding media                          | Ceramic grit (CER)          |
| Grinding medium code                    | Ceramic                     |
| Iron, sulphur and chlorine constituents | < 0.1 %                     |
| Product name attribute                  | Ø 150 mm                    |
| maximum circumferential speed           | 40 m/s                      |
| Type of product                         | Velour-backed abrasive disc |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable                                  |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable                                  |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable only under restricted conditions |                |          |
| Paint                          | suitable only under restricted conditions |                |          |
| dry                            | suitable                                  |                |          |

## Accessories

|  |            |
|--|------------|
| Hand sanding block with hook and loop fastening suitable for disc Ø 150 mm | 567857 150 |
|--|------------|

|   |            |
|---|------------|
| Hook and loop backing pad,M14 External Ø 150 mm   | 567760 150 |
| Hook and loop polishing pad,M14 External Ø 150 mm | 567762 150 |