




## Permanent magnet clamping block, with fine pole distribution, Type: MH202



### Order data

Order number	380815 MH202
GTIN	2050001854278
Item class	33S

### Description

**Version:**

Three magnetic clamping faces.

**Application:**

For profiling and machining small workpieces such as punches etc.

**Note:**

Permanent magnet, not switchable.

### Technical description

Weight	1.7 kg
Grinding allowance in pole area	14 mm
maximum angular deviation	5 degrees
Nominal clamping force	80 N/cm <sup>2</sup>
Pole pitch	4 mm
Width B	50 mm
Magnetic field height	6 mm
Type	MH202
Overall height C	50 mm
Length A	100 mm

Type of product

Magnetic clamping plate