




Permanent magnet clamping block, with fine pole distribution, Type: MH202S



Order data

Order number	380815 MH202S
GTIN	2050001922274
Item class	33S

Description

Version:

Three magnetic clamping faces.

SmCo₅ magnets permit extremely high clamping forces for materials that are difficult to machine.

Application:

For profiling and machining small workpieces such as punches etc.

Note:

Permanent magnet, not switchable.

Technical description

Pole pitch	4 mm
maximum angular deviation	5 degrees
Nominal clamping force	180 N/cm ²
Weight	1.7 kg
Width B	50 mm
Type	MH202S
Magnetic field height	6 mm
Grinding allowance in pole area	14 mm
Overall height C	50 mm

Length A	100 mm
Type of product	Magnetic clamping plate