




## Permanent magnet clamping block, with fine pole distribution, Type: MH203S



### Order data

Order number	380815 MH203S
GTIN	2050001922281
Item class	33S

### Description

#### Version:

Two magnetic clamping faces.

SmCo<sub>5</sub> magnets permit extremely high clamping forces for materials that are difficult to machine.

#### Application:

For profiling and machining small workpieces such as punches etc.

#### Note:

Permanent magnet, not switchable.

### Technical description

Width B	25 mm
Magnetic field height	6 mm
Grinding allowance in pole area	6 mm
maximum angular deviation	5 degrees
Pole pitch	4 mm
Type	MH203S
Weight	0.5 kg
Nominal clamping force	180 N/cm <sup>2</sup>
Overall height C	25 mm

Length A	100 mm
Type of product	Magnetic clamping plate