

Garant**Mini burr Z FINE – very fine, Carbide, Type: I0408****Order data**

Order number	546840 I0408
GTIN	4045197156655
Item class	51D

Description**Version:**

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank \varnothing 3 mm.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation. Also for cutting forms of internal \varnothing .

Technical description

Overall length	50 mm
Toothing grit designation	very fine
Head \varnothing	4 mm
Tooth type abbreviation	Z FINE
Shank \varnothing	3 mm
Shape	I0408
Shape description	Internal
Head length	8 mm
Series	Tooth configuration Z FINE
Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		