

Garant

GARANT Master Steel FEED solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7 (mm or inch): 6,4



Order data

Order number	122435 6,4
GTIN	4045197786692
Item class	11E

Description

Version:

3-flute drill, specially developed for **use at very high feed rates**. Extremely suitable for **machines with high power** output and stable machining conditions.

- **Special point geometry with stable cutting edges and large clearance at the centre permits very high feed rates.**
- **The patented point geometry is optimised for chip flow and generates low cutting forces with good chip breakage.**
- **With 145° point angle for low burr formation when drilling through holes.**

The **sector-leading technology of the chisel point** guarantees **optimum self-centring behaviour** and permits spot drilling on irregular surfaces. 3 guide chamfers guarantee a stable exit from the hole and an exact roundness of the hole.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

HB and HE shanks are available at the same price as HA.
For **HB shanks**: use order **No. 122436**.
For **HE shanks**: use order **No. 122435 + 129100HE**.

Standard: DIN 6537 K

Tolerance nominal Ø: h7

Number of cutting edges Z: 3

Tolerance nominal Ø: h7

recommended maximum drilling depth L_2 : 24.4 mm

Overall length L: 79 mm

Shank Ø D_s : 8 mm

Feed f in steel < 1100 N/mm²: 0.37 mm/rev.

Technical description

Number of cutting edges Z	3
Tolerance nominal \varnothing	h7
Nominal $\varnothing D_c$	6.4 mm
Shank $\varnothing D_s$	8 mm
Standard	DIN 6537 K
Overall length L	79 mm
Flute length L_c	34 mm
Feed f in steel < 1100 N/mm ²	0.37 mm/rev.
recommended maximum drilling depth L_2	24.4 mm
Series	Master Steel
Coating	TiAlN
Tool material	solid carbide
Version	4xD
Point angle	145 °
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	160 m/min	P
Steel < 750 N/mm ²	suitable	140 m/min	P
Steel < 900 N/mm ²	suitable	130 m/min	P
Steel < 1100 N/mm ²	suitable	110 m/min	P
Steel < 1400 N/mm ²	suitable	90 m/min	P
Steel < 55 HRC	suitable	60 m/min	H

INOX < 900 N/mm ²	suitable	60 m/min	M
INOX > 900 N/mm ²	suitable	50 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	40 m/min	S
GG	suitable	130 m/min	K
GGG	suitable	80 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

Services

Shank grinding Type HE

129100 HE