



## Hi5 high feed rate indexable face mill, with bore, Ø D / number of teeth Z: 52/5\_ mm

### Order data

Order number	213210 52/5_
GTIN	4045197783677
Item class	210

### Description

#### Version:

Particularly smooth-running, due to unequal spacing of the teeth.

#### Note:

Use GARANT torque screwdriver TQ No. **211750 size 2.2** with bit No. **674252 size 10IP**.

Spacing of the milling cutter's cutting edges: unequal spacing

Tool exchange: PowerCard

suitable indexable insert: POMX 0704..

### Technical description

Shank type	with bore
Milling application	
Machining strategy	
Milling head suitable for insert shape	
Tool exchange	PowerCard
Spacing of the cutters	unequal spacing
Setting angle $\kappa$	
Type of product	