



## Solid carbide high performance drill plain shank DIN 6535 HA, TiAlN, Ø DC m7: 3,8mm



### Order data

Order number	122394 3,8
GTIN	4045197418982
Item class	12E

### Description

#### Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122396**.

Form **HE**: order with **No. 122398**.

Through-coolant: no

Standard: DIN 6537 K

Tolerance nominal Ø: m7

Number of cutting edges Z: 2

recommended maximum drilling depth  $L_2$ : 18.3 mm

Tolerance nominal Ø: m7

Overall length L: 66 mm

Shank Ø  $D_s$ : 6 mm

Feed f in stainless steel < 900 N/mm<sup>2</sup>: 0.07 mm/rev.

### Technical description

Nominal Ø $D_c$	3.8 mm
Shank tolerance	h6
Flute length $L_c$	24 mm

Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.07 mm/rev.
Number of cutting edges Z	2
Tolerance nominal Ø	m7
Shank Ø D <sub>s</sub>	6 mm
Overall length L	66 mm
Standard	DIN 6537 K
recommended maximum drilling depth L <sub>2</sub>	18.3 mm
Coating	TiAlN
Tool material	Solid carbide
Version	4×D
Point angle	140 °
Shank	DIN 6535 HA to h6
Through-coolant	no
Colour ring	blue
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	140 m/min	N
Alu > 10% Si	suitable only under restricted conditions	120 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	75 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	65 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	35 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	35 m/min	M

INOX > 900 N/mm <sup>2</sup>	suitable	30 m/min	M
GG	suitable only under restricted conditions	70 m/min	K
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		