



Pair of cut-resistant heat resistant gloves ActivArmr 70-765, Glove size: 10



Order data

Order number	094622 10
GTIN	10076490485617
Item class	04P

Description

Version:

Vantage® 70-765. Kevlar® cut-resistant gloves combined with high-quality leather on the palms. With **reinforced thumbs** and seams on the back of the fingers for increased protection against cuts. Suitable for taking workpieces (e.g. sheet metal) from robot welding workplaces.

Note:

The minimum order quantity corresponds to one pack unit quantity (VPE) or a multiple thereof.
Colour: grey / green

Technical description

Glove size	10
Protection category	Category III
Type of glove	Heat protection gloves
Glove characteristics	Reinforced crook of the thumb
Glove characteristics	Flame resistance stage X
EN 388:2016	4X43D

Data sheet

EN 407	X1XXXX
Contact heat up to	200 °C
Backing material	Nylon, acrylic, Kevlar®
Coating variant	No coating
Colour	grey / green
Application	reusable
Length	235 mm
Contents	12
Washing	40 °C coloureds
Application range	All-round
Application range	Heavy Duty
Knitted technology	10G
Cut protection class	D
Weight	88.7 g
Type of product	Heat protection gloves