

Garant

GARANT Master Steel FEED solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7 (mm or inch): 8,3



Order data

| | |
|--------------|---------------|
| Order number | 122725 8,3 |
| GTIN | 4045197789327 |
| Item class | 11E |

Description

Version:

3-flute drill, specially developed for use at **very high feed rates**. Outstandingly suitable for **machines with high installed power** and stable operating conditions.

- **Special cutter geometry with stable cutting edges and large clearance at the centre enables very high feed rates.**
- **The patented tip is optimised for chip flow and generates low cutting pressure with good chip breakage.**
- **With 145° tip angle for low burr formation when drilling through holes.**

The **sector-leading technology of the chisel edge** guarantees **optimum self-centring behaviour** and permits spot drilling on irregular surfaces. 3 guide chamfers guarantee a stable exit from the hole and an exact roundness of the hole.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 122726**.

Form **HE**: order with **No. 122725 + 129100HE**.

Standard: DIN 6537

Tolerance nominal Ø: h7

Number of cutting edges Z: 3

Tolerance nominal Ø: h7

recommended maximum drilling depth L_2 : 48.6 mm

Overall length L: 103 mm

Shank Ø D_s : 10 mm

Feed f in steel < 1100 N/mm²: 0.44 mm/rev.

Technical description

| | |
|---|-------------------|
| Tolerance nominal \varnothing | h7 |
| Feed f in steel < 1100 N/mm ² | 0.44 mm/rev. |
| Shank $\varnothing D_s$ | 10 mm |
| Overall length L | 103 mm |
| Flute length L _c | 61 mm |
| Number of cutting edges Z | 3 |
| Standard | DIN 6537 |
| Nominal $\varnothing D_c$ | 8.3 mm |
| recommended maximum drilling depth L ₂ | 48.6 mm |
| Series | Master Steel |
| Coating | TiAlN |
| Tool material | solid carbide |
| Version | 6×D |
| Point angle | 145° |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|-------------|----------------|----------|
| Steel < 500 N/mm ² | suitable | 160 m/min | P |
| Steel < 750 N/mm ² | suitable | 140 m/min | P |
| Steel < 900 N/mm ² | suitable | 130 m/min | P |
| Steel < 1100 N/mm ² | suitable | 110 m/min | P |
| Steel < 1400 N/mm ² | suitable | 90 m/min | P |
| Steel < 55 HRC | suitable | 60 m/min | H |

| | | | |
|------------------------------|---|-----------|---|
| INOX < 900 N/mm ² | suitable | 60 m/min | M |
| INOX > 900 N/mm ² | suitable | 50 m/min | M |
| Ti > 850 N/mm ² | suitable only under restricted conditions | 40 m/min | S |
| GG | suitable | 130 m/min | K |
| GGG | suitable | 80 m/min | K |
| Uni | suitable | | |
| wet maximum | suitable | | |
| wet minimum | suitable | | |

Services

Shank grinding Type HE

129100 HE