

## Garant

**GARANT Master Steel SPEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 4,4mm**



### Order data

Order number	122416 4,4
GTIN	4045197790156
Item class	11E

### Description

#### Version:

Developed for use with **very high cutting speeds**. Outstandingly suitable for machines with **low installed power** and high speeds.

- **Clear reduction in cutting forces due to special cutter geometry.**
- **Coating for best wear resistance even at high process temperatures.**
- **Polished flutes for good chip clearance.**

A **slim chisel point** and the **special arrangement of the 4 guide chamfers** ensure **high positioning and alignment accuracy**. Optimised micro-geometry for increased working life and performance capability.

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

### Technical description

Flute length $L_c$	24 mm
Shank $\varnothing D_s$	6 mm
Tolerance nominal $\varnothing$	h7
Feed $f$ in steel $< 1100 \text{ N/mm}^2$	0.16 mm/rev.
Nominal $\varnothing D_c$	4.4 mm
Overall length $L$	66 mm
Number of cutting edges $Z$	2
Standard	DIN 6537 K

Shank tolerance	h6
recommended maximum drilling depth L <sub>2</sub>	17.4 mm
Series	Master Steel
Coating	TiAlN
Tool material	solid carbide
Version	4xD
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
GG	suitable	110 m/min	K
GGG	suitable	100 m/min	K
Uni	suitable		
wet maximum	suitable		