

Garant

GARANT Master Steel SPEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 7,5mm



Order data

Order number	122426 7,5
GTIN	4045197791689
Item class	11E

Description

Version:

Developed for use with **very high cutting speeds**. Outstandingly suitable for machines with **low installed power** and high speeds.

- **Clear reduction in cutting forces due to special cutter geometry.**
- **Coating for best wear resistance even at high process temperatures.**
- **Polished flutes for good chip clearance.**

A **slim chisel point** and the **special arrangement of the 4 guide chamfers** ensure **high positioning and alignment accuracy**. Optimised micro-geometry for increased working life and performance capability.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Tolerance nominal Ø	h7
Shank tolerance	h6
Flute length L_c	41 mm
Standard	DIN 6537 K
Feed f in steel < 1100 N/mm ²	0.22 mm/rev.
Overall length L	79 mm
Nominal Ø D_c	7.5 mm
Number of cutting edges Z	2

Shank $\varnothing D_s$	8 mm
recommended maximum drilling depth L_2	29.8 mm
Series	Master Steel
Coating	TiAlN
Tool material	solid carbide
Version	4xD
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	Yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	220 m/min	P
Steel < 750 N/mm ²	suitable	200 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	170 m/min	P
Steel < 1400 N/mm ²	suitable	90 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	75 m/min	M
GG	suitable	160 m/min	K
GGG	suitable	130 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

