

Garant

GARANT Master Steel SPEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 8,7mm



Order data

| | |
|--------------|---------------|
| Order number | 122716 8,7 |
| GTIN | 4045197794147 |
| Item class | 11E |

Description

Version:

Developed for use with **very high cutting speeds**. Outstandingly suitable for machines with **low installed power** and high speeds.

- **Clear reduction in cutting forces due to special cutter geometry.**
- **Coating for best wear resistance even at high process temperatures.**
- **Polished flutes for good chip clearance.**

A **slim chisel point** and the **special arrangement of the 4 guide chamfers** ensure **high positioning and alignment accuracy**. Optimised micro-geometry for increased working life and performance capability.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

| | |
|--|--------------|
| Feed f in steel < 1100 N/mm ² | 0.26 mm/rev. |
| Overall length L | 103 mm |
| Flute length L _c | 61 mm |
| Shank Ø D _s | 10 mm |
| Nominal Ø D _c | 8.7 mm |
| Standard | DIN 6537 |
| Tolerance nominal Ø | h7 |
| Number of cutting edges Z | 2 |

| | |
|---|-------------------|
| recommended maximum drilling depth L ₂ | 48 mm |
| Series | Master Steel |
| Coating | TiAlN |
| Tool material | solid carbide |
| Version | 6×D |
| Point angle | 135 degrees |
| Shank | DIN 6535 HB to h6 |
| Through-coolant | Yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Steel < 500 N/mm ² | suitable | 220 m/min | P |
| Steel < 750 N/mm ² | suitable | 200 m/min | P |
| Steel < 900 N/mm ² | suitable | 180 m/min | P |
| Steel < 1100 N/mm ² | suitable | 170 m/min | P |
| Steel < 1400 N/mm ² | suitable | 90 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 75 m/min | M |
| GG | suitable | 160 m/min | K |
| GGG | suitable | 130 m/min | K |
| Uni | suitable | | |
| wet maximum | suitable | | |
| wet minimum | suitable | | |