



## Socket set and combination spanners, 1/2 inch square drive 47 pieces



### Order data

Order number	638561
GTIN	4018754261178
Item class	63A

### Description

#### Version:

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120**.

#### Application:

For hexagon head screws / nuts with thread M5 – M22. Spark plugs 16 and 20.8 mm. Hexagon socket head screws with thread M5 – M12.

#### Material:

Chrome alloy steel, chrome-plated.

#### Supplied with:

Socket single hexagon: 19 pcs. No. 642200  
size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19;  
21; 22; 24; 27; 30; 32; 34

Spark plug sockets: 2 pcs. No. 642450  
size 16; 20.8

Screwdriver sockets, hexagon: 7 pcs. No. 643200  
size 4; 5; 6; 7; 8; 10; 12

T-handle: 1 pc. No. 641300 size 300

Extensions: 3 pcs. No. 641000  
size 75; 130; 255

Universal joint: 1 pc. No. 641600 size 1/2

Ratchet: 1 pc. No. 640100 size 1/2  
 Combination spanner: 13 pcs. No. 613500  
 size 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24  
 Presented in: ABS plastic box

## Technical description

Width across flats range, hexagon wrenches	4-12 mm
Number of pieces	47
Width across flats range, hexagon sockets	8-34 mm
Width across flats	metric
Drive profile	Hexagon screwdriver
Drive profile	Hexagon socket
Drive profile	Bi-hex socket
Square drive	1/2 in
Packaging	ABS plastic box
Length	481 mm
Width	288 mm
Height	82 mm
Type of product	Socket spanner

## Accessories

Combination spanner Width across flats 10 mm	613500 10
Combination spanner Width across flats 11 mm	613500 11
Combination spanner Width across flats 12 mm	613500 12
Combination spanner Width across flats 13 mm	613500 13
Combination spanner Width across flats 14 mm	613500 14
Combination spanner Width across flats 15 mm	613500 15
Combination spanner Width across flats 16 mm	613500 16
Combination spanner Width across flats 17 mm	613500 17

Combination spanner Width across flats 18 mm	613500 18
Combination spanner Width across flats 19 mm	613500 19
Combination spanner Width across flats 21 mm	613500 21
Combination spanner Width across flats 22 mm	613500 22
Combination spanner Width across flats 24 mm	613500 24
Extension, 1/2 inch overall length 130 mm	641000 130
Extension, 1/2 inch overall length 255 mm	641000 255
Extension, 1/2 inch overall length 75 mm	641000 75
T-handle, 1/2 inch overall length 300 mm	641300 300
Universal joint, 1/2 inch Type 1/2	641600 1/2
Hexagon socket, 1/2 inch Width across flats 10 mm	642200 10
Hexagon socket, 1/2 inch Width across flats 11 mm	642200 11
Hexagon socket, 1/2 inch Width across flats 12 mm	642200 12
Hexagon socket, 1/2 inch Width across flats 13 mm	642200 13
Hexagon socket, 1/2 inch Width across flats 14 mm	642200 14
Hexagon socket, 1/2 inch Width across flats 15 mm	642200 15
Hexagon socket, 1/2 inch Width across flats 16 mm	642200 16
Hexagon socket, 1/2 inch Width across flats 17 mm	642200 17
Hexagon socket, 1/2 inch Width across flats 18 mm	642200 18
Hexagon socket, 1/2 inch Width across flats 19 mm	642200 19
Hexagon socket, 1/2 inch Width across flats 21 mm	642200 21
Hexagon socket, 1/2 inch Width across flats 22 mm	642200 22
Hexagon socket, 1/2 inch Width across flats 24 mm	642200 24
Hexagon socket, 1/2 inch Width across flats 27 mm	642200 27
Hexagon socket, 1/2 inch Width across flats 30 mm	642200 30
Hexagon socket, 1/2 inch Width across flats 32 mm	642200 32
Hexagon socket, 1/2 inch Width across flats 34 mm	642200 34
Hexagon socket, 1/2 inch Width across flats 8 mm	642200 8
Hexagon socket, 1/2 inch Width across flats 9 mm	642200 9

Bi-hexagon spark plug socket, 1/2 inch Width across flats 16 mm	642450 16
Bi-hexagon spark plug socket, 1/2 inch Width across flats 20,8 mm	642450 20,8
Hexagon bit socket, 1/2 inch Hexagon 10 mm	643200 10
Hexagon bit socket, 1/2 inch Hexagon 12 mm	643200 12
Hexagon bit socket, 1/2 inch Hexagon 4 mm	643200 4
Hexagon bit socket, 1/2 inch Hexagon 5 mm	643200 5
Hexagon bit socket, 1/2 inch Hexagon 6 mm	643200 6
Hexagon bit socket, 1/2 inch Hexagon 7 mm	643200 7
Hexagon bit socket, 1/2 inch Hexagon 8 mm	643200 8