



## LED cordless work lamp, Type: 42



### Order data

Order number	081254 42
GTIN	5708997354438
Item class	08C

### Description

#### Version:

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption, long working life.**
- **Certified for exterior use and for use in humid environments.**

**NOVA work lamps** with integral carrying handle. High-performance COB-LED with 5-step dimmer function, pivoting. Due to the dual system, can be used both as a mobile cordless floodlight, and also with mains cable. Charge status display, remaining time display, dimmable in 5 stages.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Including battery charger.

### Technical description

Battery capacity	5.2 Ah
Number of rechargeable batteries contained	1

IP Index of Protection	IP 67
Battery voltage	11.1 V
Type of rechargeable battery	Lithium-ion
Illumination	600 - 6000 lm
ATEX zone	no
Power supply	Rechargeable battery-powered
Illumination time	1 - 12 h
Overall width	92 mm
Overall length	275 mm
Overall height	275 mm
CRI value	80
Weight	2600 g
Power consumption	42 W
Manufacturer's designation	NOVA 5K 42W
Type of product	Work lamp