

## Boring bar head for disc turrets, Type A, Clamping Ø: 25 mm



### Order data

Order number	319162 25
GTIN	4251414900387
Item class	38T

### Description

#### Version:

The first successful introduction of a tool mounting design which can be used on both disc turrets and radial turrets. Irrespective of the alignment method in use. Modular system configuration.

#### Advantage:

- **All tools with direct internal coolant supply connection.**
- **Cost reduction via efficient stock-holding of bearings.**
- **Higher productivity due to improved positioning.**

#### Note:

Suitable for vibration-damped boring bars No. 264902 – 264908, No. 264910 – 264922 or tools with plain shank (such as: solid carbide boring bars Ø 10 mm).  
Length L: 100 mm

### Technical description

Clamping Ø	25 mm
Length L	100 mm
Adapter	Type A

