

**Circular saw blade expert for Steel, Blade Ø D: 305mm****Order data**

Order number	583910 305
GTIN	3165140737739
Item class	54B

**Description****Version:**

Precision saw blade with high-strength, **noise and vibration suppressing blade body**. The tensioning ring incorporated ensure stability of the shape in all temperature ranges. The **coating** prevents adhesions, keeps the saw blade cool and protects it against corrosion. **Precision-ground carbide teeth** ensure a long working life and best quality of cut.

**Application:**

For **machining steel**. Special anchoring of the carbide teeth in the base blade prevents teeth breaking off. Tooth form: Trapezoidal flat teeth (with chamfer), neutral rake angle. For tenon saws and mitre saws.

**Note:**

**Further circular saw blades can be found in Group 17.**

**Technical description**

Ø	305 mm
Bore Ø	25.4 mm
Number of teeth	60

Width of cut B	2.6 mm
Type of product	Circular saw blade