



## LED machine lamp round, Type: 250mm



### Order data

Order number	081435 250
GTIN	4260131235498
Item class	08C

### Description

#### Version:

Sturdy LED machine lamps in an **aluminium casing**, with a satinised acrylic lens for **homogeneous 160-degree illumination**.

- **Low-reflection, non-dazzle and non-flicker.**
- **For connection to a 24 V mains adapter or 24 V machine control system.**

Rotatable.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

With rubber-clad magnets, mains adapter.

### Technical description

Illumination	900 lm
Bulb	LED module
Light output	9 W

Power supply	Mains operated
ATEX zone	no
Overall length	250 mm
Head Ø	40 mm
IP Index of Protection	IP 67
Type of product	Machine lamp