



## Torque screwdriver with scale, maximum torque: 120cNm



### Order data

Order number	659939 120
GTIN	4560138455067
Item class	66F

### Description

#### Version:

Torque screwdrivers with over-torque protection for different applications from series production to maintenance work. With a locking mechanism that prevents adjustment of the torque when in use. The hexagon lock shape prevents rolling away. Setting by using micrometer scale. With synthetic resin handle for better grip.

#### Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use. The trigger mechanism is unavailable for tightening left-handed threads.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

### Technical description

Torque measuring accuracy	±3 %
Scale graduation, 1 graduation =	1 cNm
Display	analogue
maximum torque	120 cNm
Ø	24 mm
Bit socket	F 6.3

Torque range	20 - 120 cNm
Torque range	0.2 - 1.2 Nm
Weight	160 g
Standard	DIN EN ISO 6789
Reversible reading	Nm
Measurement process	Torque
Setting the trigger value	with adjustment scale
Feedback	triggering
Overall length L	130 mm
Adjustable trigger value	adjustable
Trigger principle	mechanical slip clutch
Connection format	Bit holder 1/4 inch
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	optisk
Release signalling	akustisk
Type of product	Torque screwdriver

## Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------