



## Torque screwdriver with scale, maximum torque: 60cNm



### Order data

Order number	659939 60
GTIN	4560138455005
Item class	66F

### Description

#### Version:

Torque screwdrivers with over-torque protection for different applications from series production to maintenance work. With a locking mechanism that prevents adjustment of the torque when in use. The hexagon lock shape prevents rolling away. Setting by using micrometer scale. Profiled light metal handle.

#### Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use. The trigger mechanism is unavailable for tightening left-handed threads.

#### Standard:

Geprüft nach DIN EN ISO 6789.

#### Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

### Technical description

maximum torque	60 cNm
Ø	20 mm
Display	analogue
Scale graduation, 1 graduation =	0.5 cNm
Torque measuring accuracy	±3 %
Bit socket	F 6.3

Torque range	10 - 60 cNm
Torque range	0.1 - 0.6 Nm
Standard	DIN EN ISO 6789
Setting the trigger value	with adjustment scale
Feedback	triggering
Overall length L	110 mm
Connection format	Bit holder 1/4 inch
Weight	80 g
Trigger principle	mechanical slip clutch
Adjustable trigger value	adjustable
Reversible reading	Nm
Measurement process	Torque
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	optisk
Release signalling	akustisk
Measurement technology	mechanical
Type of product	Torque screwdriver

## Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------