



Torque screwdriver with scale, maximum torque: 30cNm



Order data

Order number	659939 30
GTIN	4560138455852
Item class	66F

Description

Version:

Torque screwdrivers with over-torque protection for different applications from series production to maintenance work. With a locking mechanism that prevents adjustment of the torque when in use. The hexagon lock shape prevents rolling away. Setting by using micrometer scale. Profiled light metal handle.

Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use. The trigger mechanism is unavailable for tightening left-handed threads.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Direction of tightening: Right-hand tightening

Torque measuring accuracy: $\pm 3\%$

Bit socket: F 6.3

Test certificate: Manufacturer's test certificate

Calibration: O1

Torque measuring accuracy: $\pm 3\%$

Overall length L: 100 mm

Torque range: 4 - 30 cNm

Torque range: 0.04 - 0.3 N·m

Scale graduation, 1 graduation =: 0.2 cNm

Ø: 16 mm

Technical description

Scale graduation, 1 graduation =	0.2 cNm
maximum torque	30 cNm
Torque measuring accuracy	±3 %
Display	analogue
Ø	16 mm
Bit socket	F 6.3
Torque range	4 - 30 cNm
Torque range	0.04 - 0.3 N·m
Reversible reading	Nm
Weight	50 g
Trigger principle	mechanical slip clutch
Adjustable trigger value	adjustable
Measurement process	Torque
Connection format	Bit holder 1/4 inch
Setting the trigger value	with adjustment scale
Feedback	triggering
Overall length L	100 mm
Standard	DIN EN ISO 6789
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	optisk
Release signalling	akustisk
Measurement technology	mechanical
Type of product	Torque screwdriver

Services

Labellinglaser-etched Type

018940

CalibrationTorque wrench maximum torque 400 N·m

020010 400